

# **N8500 Spectrometer**





## Overview

---

High-resolution spark emission spectrometer for material analysis and determination of chemical compositions in metals. The FL 8500 Fluorescence Spectrophotometer has superior accuracy for right first time results even on diluted or small sample amounts. It is exceptionally sensitive with a Raman S/N ratio of 5,000:1 (RMS), which allows for fast measurements of. Features and Benefits include: Sensitivity, high performance R928 PMT detector combined with PerkinElmer optics ensures optimum performance.



## N8500 Spectrometer

---



### NCS S 8500-N

This page shows NCS color S 8500-N. This NCS color is in the S 7000 - S 9000 category, part of the NCS color system.

[Contact Us](#)

### FP-8500 Spectrofluorometer

FP-8500 Spectrofluorometer The FP-8500 Spectrofluorometer is a high performance spectrofluorometer with an optimized optical design for very low stray light and a dynamic range of up to 6.5 orders of

[Contact Us](#)



### FL 8500 Fluorescence Spectrophotometer with

FL 8500 Fluorescence Spectrophotometer with Spectrum FL Software The FL 8500 Fluorescence Spectrophotometer uses a continuous wave excitation source for

[Contact Us](#)



### FP-8000 Series Spectrofluorometer


Electronic signature Audit trail A unique, single platform software package for any JASCO spectroscopy system Spectra t Manager™ T II and CFR - JASCO is the first manufacturer to develop a powerful,



### Spectrofluorometer

Drivers are included to control each spectroscopy instrument and parameter dialogs allow easy editing of pre-saved parameter files. Data acquired from each instrument is automatically loaded into the


[Contact Us](#)



### TS8500 spectrophotometer\_3nh Spectrophotometer, Colorimeter,

TS8500 is a benchtop grating spectrophotometer which is developed by 3nh independently with core technology. It uses a dual-array CMOS image sensor to have high sensitivity and a wider spectral

[Contact Us](#)



### Natural Color System S 9000-N vs S 8500-N side by side comparison

S 9000-N vs S 8500-N This comparison juxtaposes two swatches drawn from the same colour framework. The first sample is identified by code S 9000-N and forms part of the NCS 1950 Index

[Contact Us](#)






### Fluorescence spectrometers from PerkinElmer

PerkinElmer has launched the FL 6500(TM) pulse xenon and FL 8500(TM) continuous wave fluorescence spectrometers. The FL 8500 fluorescence

[Contact Us](#)



### TS8500S spectrophotometer\_3nhlab

TS8500S is a benchtop grating spectrophotometer which is developed by 3nh independently with core technology. It uses a dual-array CMOS image sensor to have high sensitivity and a wider spectral

[Contact Us](#)

### Perkin-Elmer FL 6500 Installation Instructions Manual

View and Download Perkin-Elmer FL 6500 installation instructions manual online. Low Temperature Cell Holder. FL 6500 laboratory equipment pdf manual

[Contact Us](#)



### S 8500-N

S 8500-N - Neutrale Farbtöne - Produkte in diesem Farbton finden , Sikkens Probiere jetzt die Sikkens Expert App Mehr erfahren

[Contact Us](#)



## Fluorescence Spectro FL 6500 Pulse and FL8500

SPECIFICATIONS Fluorescence Spectroscopy FL 6500(TM) - Pulse Fluorescence Spectrometer and FL 8500(TM) - Continuous Wave Fluorescence

[Contact Us](#)



## FP-8500 Spectrofluorometer, 200

FP-8500 Spectrofluorometer, 200 - 750 nm, JASCO (CAT#: STEM-LE-0061-LC)

[Contact Us](#)

## NCS S 8500-N: Understanding the Color, Examples, and Compatibility

Discover everything about the NCS S 8500-N color including its definition, examples, compatibility with other colors, NCS standard

[Contact Us](#)



Grid Cable for marine and offshore applications



## FL 8500 Fluorescence Spectrophotometer with Spectrum FL Software

The FL 8500 Fluorescence Spectrophotometer has superior accuracy for right first time results even on diluted or small sample amounts. Rapid scanning increases sample throughput and maximizes your

[Contact Us](#)



## Fluorometer

A comprehensive range of four individual models of fluorometer in the FP-8050 Series for high quality spectroscopic measurement

[Contact Us](#)



## PerkinElmer Launches FL 6500(TM) and FL 8500(TM)

FL 8500 Continuous Wave fluorescence spectrometer PerkinElmer, Inc., a global leader committed to innovating for a healthier world, today

[Contact Us](#)

## AC-N8500 UNIVER Stock

UNIVER AC-N8500 NAMUR VALVES PDF -- Type: AC -N ISO 4762 Mixed commutation system (spool-poppet)- High flow rate- Quick response time- High

[Contact Us](#)



## Fluorescence spectrophotometer

Find out all of the information about the PerkinElmer product: fluorescence spectrophotometer FL 8500. Contact a supplier or the parent company directly to


[Contact Us](#)



### FL 8500 Fluorescence Spectrometer , Labware Group

It allows high-sensitivity measurements at scan speeds of up to 60,000 nm/min.

[Contact Us](#)



### S 8500-N - NCS Colour

Enhance your colour projects with NCS - Find your NCS colour codes and explore our digital and physical colour solutions and education to transform your colour

[Contact Us](#)

### Fluorescence Spectrometers Specifications

Spectrometer Specification \*1 : Minimum Signal-to-Noise ratio of Raman band of water, excitation 350 nm, band width Ex 5 nm Em 5 nm (FP-8650: Ex 5 nm Em 5 nm)

[Contact Us](#)

OEM/ODM  
CUSTOMIZATION AVAILABLE




Full product customization



Structure customization



Brand customization



Packaging design



### TS8500 spectrophotometer-3nh

TS8500 is a benchtop grating spectrophotometer which is developed by 3nh independently with core technology. It uses a dual-array CMOS image sensor to have high sensitivity and a wider spectral

[Contact Us](#)



**Product: DSC 8500**

The DSC 8500 is a double-furnace DSC, featuring our second-generation HyperDSC technology. Now you can gain unlimited insight into the structure, properties and performance of your materials.

[Contact Us](#)



**FL 8500 Fluorescence Spectrophotometer :  
Quote,**

The FL 8500 Fluorescence Spectrophotometer uses a continuous wave excitation source for high sensitivity measurements at scan speeds up to 60,000 nm/min.

[Contact Us](#)

**PerkinElmer**

The FL 8500 instrument features and benefits include: Continuous Wave Fluorescence Spectrometer Uses a Xenon Arc (150 W) lamp source Greater sensitivity and wavelength scan speed.

[Contact Us](#)



**FL 8500 Fluorescence Spectrometer ,  
Labware Group**

FL 8500 fluorescence spectrometer features continuous wave excitation. It allows high-sensitivity measurements at scan speeds of up to 60,000 nm/min. FL 8500's

[Contact Us](#)



## Application eBook

Enzyme kinetics probed by fluorescence spectroscopy Enzyme activity is frequently investigated in the medicinal, biochemistry, and food science research fields to elucidate reaction rates and the affinity

[Contact Us](#)



## Farbton S 8500-N bei Prosol

über 80 Standorte Mit über 80 Standorten in Deutschland und Österreich - auch in Ihrer Nähe.

[Contact Us](#)



## Spectrofluorometers

The FP-8050 Series of spectrofluorometers includes four different instruments that provide solutions for the broadest range of applications including QC,

[Contact Us](#)



## FP-8000 Series

Performance Innovation Reliability In 1967, JASCO launched the FP-1, which was the first in a long line of spectrofluorometers. The FP-8000 Series is the latest comprehensive range of instruments,

[Contact Us](#)





## FL 8500

The FL 8500 from PerkinElmer Inc is a Continuous Wave Fluorescence Spectrometer that operates at a wavelength of 200 nm - 900 nm. It has a wavelength accuracy of 0.5 nm, wavelength reproducibility

[Contact Us](#)



## BFP-1706\_170612


Drivers are included to control each spectroscopy instrument and parameter dialogs allow easy editing of pre-saved parameter files. Data acquired from each instrument is automatically loaded into the

[Contact Us](#)

## ASD LabSpec , NIRS Spectrometers

ASD LabSpec spectrometers offer laboratory-grade spectral performance in a robust, portable design suitable for benchtop analysis

[Contact Us](#)



## FP-8500 Spectrofluorometer

The FP-8500 Spectrofluorometer is a high performance spectrofluorometer with an optimized optical design for very low stray light and a dynamic range of up to 6.5 orders of magnitude. It is

[Contact Us](#)



### Match of Natural Color System(TM) S 8500-N

Natural Color System S 8500-N precisely matched in spray paint, brush in cap bottles, paint pens, house paint, and other sizes for touch up or painting applications.

[Contact Us](#)



### PerkinElmer FL-8500 Fluorescence Spectrophotometer


The FL 8500 Fluorescence Spectrophotometer has superior accuracy for right first time results even on diluted or small sample amounts. Rapid scanning increases

[Contact Us](#)

### Products - NCS Germany

A sequential wavelength dispersive X-ray fluorescence spectrometer for comprehensive elemental analysis in geology, materials science and

[Contact Us](#)



## Contact Us

For datasheets, pricing, or custom fiber access solutions, please visit:  
<https://www.frindel.es>